



EE861



**IP55**

## IP55 Motion Detector Comfort 220° Anthracite

### Technical characteristics

#### Architecture

Bus system Without

#### Functions

Function Presence simulation ; can be used as a single unit, main device or extension unit

#### Main electrical features

Frequency 50/60 Hz

#### Dimensions

Height of installed product 2.5 m

#### Power supply

Supply voltage 230 V +10% / -15%

#### Detection

Detection angle 220 °

#### Materials

Material plastic

#### Lighting control

Brightness measurement range 5 / 1000 Lux

#### Installation, mounting

Maximum Mounting Height 4 m

#### Connection

Type of connection with screw terminals

#### Settings

Setting with potentiometers for setting the response brightness and delay time without dismantling

#### Scope of delivery

Component with fitting material

#### Equipment

Remote controllable EE806

Angle of horizontal detection 220 °

#### Use conditions

Operating temperature -20...55 °C

Subject to technical modifications

