



EE870



**IP55**

## IP55 Motion Detector Comfort 220/360° White

### Technical characteristics

#### Architecture

Bus system Without

#### Functions

Function Presence simulation ; can be used as a single unit, main device or extension unit

#### Main electrical features

Frequency 50/60 Hz

#### Dimensions

Height of installed product 2.5 m

#### Power

Incandescent bulb power 2300 W

#### Power supply

Supply voltage 230 V AC

#### Detection

Detection angle 220 / 360 °

Detection angle 360 °

#### Materials

Colour white

#### Lighting control

Brightness measurement range 5 / 1000 Lux

#### Installation, mounting

Maximum Mounting Height 4 m

#### Connection

Connection type quick connect

Type of contacts contact floating

Type of connection with screw terminals

#### Settings

Time delayed range 5s to 30 min

Setting with potentiometers for fine adjustment of the response brightness, sensitivity and delay time

#### Scope of delivery

Component

with fitting material

---

**Safety**

Protection class

isol.class II

Protection

with crawl-under protection

---

**Use conditions**

Operating temperature

-20...55 °C