



EE871



**IP55**

**IP55 Motion Detector Comfort 220/360° Anthracite**

**Technical characteristics**

**Architecture**

Bus system Without

**Functions**

Function Presence simulation ; can be used as a single unit, main device or extension unit

**Main electrical features**

Frequency 50/60 Hz

**Dimensions**

Height of installed product 2.5 m

**Power**

Incandescent bulb power 2300 W

**Power supply**

Supply voltage 230 V AC

**Detection**

Detection angle 220 / 360 °

**Lighting control**

Brightness measurement range 5 / 1000 Lux

**Installation, mounting**

Maximum Mounting Height 4 m

**Connection**

Connection type quick connect

Type of contacts contact floating

Type of connection with screw terminals

**Settings**

Time delayed range 5s to 30 min

Setting with potentiometers for fine adjustment of the response brightness, sensitivity and delay time

**Scope of delivery**

Component with fitting material

**Safety**

Protection class isol.class II

Protection

with crawl-under protection

**Use conditions**

---

Operating temperature

-20...55 °C