



EE871



IP55



IP55 Motion Detector Comfort 220/360° Anthracite

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Power

Incandescent bulb power 2300 W

Detection

Detection angle 220 / 360 °

Materials

Colour charcoal

Lighting control

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Connection

Type of connection with screw terminals

Settings

Setting with potentiometers for fine adjustment of the response brightness, sensitivity and delay time

Scope of delivery

Component with fitting material

Safety

Protection index IP IP55

Protection class isol.class II

Use conditions

Operating temperature -20...55 °C