




EEN101



IP20

Twilight switch 1 channel, 1M, flush mounted cell

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	65 mm
Height of installed product	83 mm
Width of installed product	17.8 mm

Length

Maximum connection distance between receiver and transmitter	100m
--------------------------------------------------------------	------

Power

Max. power with fluo uncompensated lamps	1000 VA
Power consumed	0.3 VA
Power consumption (operation)	300 mW
Incandescent bulb power	2300 W
Total power loss under IN	0.3 W
Power dissipation per coil	0.3 W

Endurance

Electrical endurance cycles with incandescent lighting	7500
--------------------------------------------------------	------

Lighting control

Brightness measurement range	5 / 2000 Lux
------------------------------	--------------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1000 VA
Max. power fluo. duo lamp comp. series	1000 W

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1,5 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 6mm ²
Number of contacts	1

Type of contacts

contact floating

Type of connection

with screw terminals

Settings

Setting

Switch-on/switch-off delay continuously adjustable
via potentiometer