



EG010



Daily time switch 1 channel, digital, 1 module

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Depth of installed product	64 mm
Height of installed product	92 mm
Width of installed product	18 mm

Power

Power consumed	1 VA
Total power loss under IN	1 W
Power dissipation per coil	1 W

Battery

Power reserve [years]	≈ 3 a
Charging time of the power reserve in hours	0

Incandescent bulbs control

Max. power with incandescent lamps	1000 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	24H

Equipment

Number of channels	1
Supply failure reserve	3 years
Use	
Cycle	daily
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-10...50 °C
Working accuracy	1