



EG103



1 channel dig time switch weekly cycle

Technical characteristics

Functions

Function	Keylock by means of blocking key
----------	----------------------------------

Configuration

Switch mode	change-over contact
-------------	---------------------

Main electrical features

Rated operational voltage Ue	195 / 230 / 264 V
Frequency	50 Hz

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

Power

Power consumed	6 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

Battery

Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.

Equipment

Number of channels	1
Supply failure reserve	5 years
Use	
Cycle	weekly
Use conditions	
Operating temperature	-5...45 °C
Working accuracy	1,5