



EG103



1 channel dig time switch weekly cycle

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Main electrical features

Rated operational voltage Ue	195 / 230 / 264 V
Frequency	50 Hz

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

Power

Power consumed	6 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

Battery

Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	1 / 16mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.

Equipment

Number of channels	1
Supply failure reserve	5 years

Use

Cycle

weekly

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-5...45 °C

Working accuracy

1,5