



EG103



## 1 channel dig time switch weekly cycle

### Technical characteristics

#### Functions

Function	Keylock by means of blocking key
----------	----------------------------------

#### Main electrical features

Rated operational voltage U <sub>e</sub>	195 / 230 / 264 V
Frequency	50 Hz

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

#### Power

Power consumed	6 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

#### Battery

Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Connection

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover

#### Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.

#### Equipment

Number of channels	1
Supply failure reserve	5 years

#### Use

Cycle

weekly

### Safety

Protection index IP

IP20

### Use conditions

Operating temperature

-5...45 °C

Working accuracy

1,5