



EG103V



IP20

Weekly time switch 1 channel, 12/24V, digital, 2 modules

Technical characteristics

Functions

Function	Presence simulation ; Keylock by means of blocking key ; with pulse function
----------	--

Configuration

Switch mode	change-over contact
-------------	---------------------

Main electrical features

Rated operational voltage Ue	12 / 24 V
Frequency	50 Hz

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

Power

Power consumed	0.8 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W

Battery

Charging time of the power reserve in hours	0
---	---

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.

Equipment

Number of channels	1
Supply failure reserve	5 years

Use

Cycle	weekly
-------	--------

Use conditions

Working accuracy	1,5
------------------	-----