



CEA225U

RCCB 2P 25A 100mA A Class

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	100 mA
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA

Electric current / temperature

Rating current 30°C	25 A
---------------------	------

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

Power

Total power loss under IN	1.3 W
---------------------------	-------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1 / 25mm ²
Type of connection	with screw

Standards

Standard text

BS 61008-1 ; EN 61008-1

Safety

Residual current type

A

Use conditions

Operating temperature

-25...40 °C