



CEA240U

RCCB 2P 40A 100mA A Class

Technical Characteristics

Neutral position	right
Number of poles	2 P
Fixing mode	DIN rail type O (symmetrical)
Rated operational voltage Ue	230 V
Frequency	50 Hz
Rated current	40 A
Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V
Rated residual operating current	100 mA
Breaking and opening capacity	1500 A
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA
Rating current 30°C	40 A
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm
Total power loss under IN	3.2 W
Residual current trip mode	Undelayed
Electric endurance in number of cycles	2000
Number of mechanical operations	4000
Number of modules	2
Tightening torque	2,8Nm
Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1 / 25mm ²
Type of connection	with screw
Standard text	BS 61008-1 EN 61008-1
European directive WEEE	concerned
Protection index IP	IP20
Residual current type	A
Operating temperature	-25...40 °C