



EG203E



Digital time switch weekly cycle 2 channels Evolution

Technical characteristics

Functions

Function	Keylock by means of blocking key
----------	----------------------------------

Main electrical features

Rated operational voltage Ue	195 / 230 / 265 V
Frequency	50 Hz

Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	35 mm

Power

Power consumed	6 VA
Total power loss under IN	4 W
Power dissipation per coil	0.5 W

Battery

Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Number of contacts	2
Type of contacts	2 changeovers

Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	2X7D.

Equipment

Number of channels	2
Supply failure reserve	5 years

Use

Cycle

weekly

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-5...45 °C

Working accuracy

1,5