



EG293B



## Yearly time switch 2 channels, digital, 4 modules

### Technical characteristics

#### Architecture

Fixing mode Din-Rail

#### Functions

Function Presence simulation ; Keylock via PIN code ; with operating hours meter ; with pulse function

#### Configuration

Switch mode 2 x change-over contact

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

#### Dimensions

Depth of installed product 69 mm

Height of installed product 90 mm

Width of installed product 70 mm

#### Power

Power consumed 2 VA

Total power loss under IN 2 W

#### Battery

Power reserve [years]  $\approx$  5 a

#### Incandescent bulbs control

Max. power with incandescent lamps 1500 W

#### Installation, mounting

Mounting type din-Rail

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of connection quick connect

Number of contacts 2

Type of contacts 2 changeover + 2NO

Type of connection with QuickConnect plug-in terminals

#### Settings

Summer / Winter time change automatic

Shortest switching time	1 mn
Type of programming	digital, with programming key
Programming cycle	yearly
<b>Equipment</b>	
Number of channels	2
Supply failure reserve	5 years
<b>Use</b>	
Cycle	yearly
<b>Safety</b>	
Protection index IP	IP20
<b>Use conditions</b>	
Operating temperature	-10...50 °C
Working accuracy	+ 0,2 s / 24h