




EG293B



Yearly time switch 2 channels, digital, 4 modules

Technical characteristics

Functions

Function	Presence simulation ; Keylock via PIN code ; with operating hours meter ; with pulse function
----------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Dimensions

Depth of installed product	69 mm
Height of installed product	90 mm
Width of installed product	70 mm

Power

Power consumed	2 VA
Total power loss under IN	2 W

Battery

Power reserve [years]	≈ 5 a
-----------------------	-------

Incandescent bulbs control

Max. power with incandescent lamps	1500 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of connection	quick connect
Number of contacts	2
Type of contacts	2 changeover + 2NO
Type of connection	with QuickConnect plug-in terminals

Settings

Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital, with programming key
Programming cycle	yearly

Equipment

Number of channels	2
Supply failure reserve	5 years
Use	
Cycle	yearly
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-10...50 °C
Working accuracy	+ 0,2 s / 24h