



CF285U

## RCCB 2P 100A 300mA A

### Technical characteristics

#### Architecture

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)

#### Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

#### Voltage

Rated impulse withstand voltage	4000 V
---------------------------------	--------

#### Electric current

Rated residual operating current	300 mA
Rated conditional short-circuit current $I_{nc}$ according to EN 61008-1	6 kA

#### Electric current / temperature

Rating current 30°C	100 A
---------------------	-------

#### Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

#### Power

Total power loss under IN	14.3 W
---------------------------	--------

#### Tripping

Short-time delayed tripping	No
-----------------------------	----

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

#### Installation, mounting

Tightening torque	3,3Nm
-------------------	-------

#### Connection

Type of connection	with screw
--------------------	------------

**Equipment**

---

Can be accessorized Yes

**Standards**

---

Standard text EN 61008-1

European directive WEEE concerned

**Safety**

---

Protection index IP IP20

Residual current type A

**Use conditions**

---

Operating temperature -25...40 °C