




EGN103



## 1 channel digital time switch weekly cycle

### Technical characteristics

#### Main electrical features

Rated operational voltage $U_e$	230 V AC
Frequency	50/60 Hz
Nominal voltage	230 V
Type of supply voltage	AC

#### Dimensions

Depth of installed product	61.6 mm
Height of installed product	90 mm
Width of installed product	35.8 mm

#### Power

Power consumed	0.39 VA
Power consumption (operation)	350 mW

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	400 W
Max. power fluo. duo lamp comp. series	1000 W

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminal

#### Settings

Shortest switching time	1 mn
-------------------------	------

#### Equipment

Type of programmable thermostat	Digital
Number of channels	1
Supply failure reserve	5 years

