



EH011



IP20

Daily time switch 1 channel, 1 modules with reserve

Technical characteristics

Functions

Power reserve	≈ 200 h
---------------	---------

Main electrical features

Rated operational voltage Ue	210 / 230 V
Frequency	50 Hz

Dimensions

Depth of installed product	60 mm
Height of installed product	80 mm
Width of installed product	18 mm

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

Battery

Charging time of the power reserve in hours	120
---	-----

Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Number of contacts	1
Type of contacts	1 changeover

Settings

Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Programming cycle	24H
Setting	Setting via day dial

Equipment

Number of channels	1
Supply failure reserve	200 h
Use	
Cycle	daily
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-10...55 °C
Working accuracy	1