



EH110



IP20

Daily time switch 1 channel, analog, 3 modules

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Switch mode	change-over contact, usable as NC or NO
-------------	---

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Depth of installed product	54 mm
Height of installed product	90 mm
Width of installed product	65 mm

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Programming cycle	24H

Equipment

Number of channels	1
--------------------	---

Supply failure reserve

without

Use

Cycle

daily

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-10...45 °C

Working accuracy

1