



EH110



**IP20**

## Daily time switch 1 channel, analog, 3 modules

### Technical characteristics

#### Main electrical features

Frequency	50 Hz
-----------	-------

#### Dimensions

Depth of installed product	54 mm
Height of installed product	90 mm
Width of installed product	65 mm

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

#### Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Type of connection	with screw
Number of contacts	1
Type of connection	with screw terminals

#### Settings

Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Programming cycle	24H

#### Equipment

Number of channels	1
Supply failure reserve	without

#### Use

Cycle	daily
-------	-------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...45 °C
Working accuracy	1