




CFA690



RCCB 3P+N 125A 300mA A

Technical characteristics

Architecture

Neutral position	right
Number of poles	4 P
Type of pole	3P+N

Main electrical features

Rated operational voltage Ue	240 / 415 V
Frequency	50/60 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Max operating voltage	456 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	300 mA
Rated conditional short-circuit current Inc according to EN 61008-1	10 kA

Electric current / temperature

Rating current 30°C	125 A
---------------------	-------

Dimensions

Depth of installed product	70 mm
Height of installed product	85 mm
Width of installed product	72 mm

Power

Total power loss under IN	29.2 W
---------------------------	--------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Equipment

Quick connect	no
Can be accessorized	Yes

Standards

Standard text

EN 61008-1 ; IEC 61008-1

Safety

Residual current type

A

Use conditions

Operating temperature

-25...40 °C