



EH111



Time switch daily cycle with reserve

Technical characteristics

Functions

Power reserve	≈ 200 h
---------------	---------

Configuration

Switch mode	change-over contact, usable as NC or NO
-------------	---

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	54 mm

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

Battery

Charging time of the power reserve in hours	120
---	-----

Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog

Programming cycle	24H
Setting	Setting via day dial
Equipment	
Number of channels	1
Supply failure reserve	200 h
Use	
Cycle	daily
Use conditions	
Operating temperature	-10...55 °C
Working accuracy	1