



EH210



## Daily time switch without reserve with clock hands, 2 modules

### Technical characteristics

#### Configuration

Switch mode change-over contact, usable as NC or NO

#### Main electrical features

Frequency 50/60 Hz

#### Dimensions

Depth of installed product 58 mm

Height of installed product 90 mm

Width of installed product 36 mm

#### Power

Power consumed 0.5 VA

Power consumption (operation) 0.5 VA

Total power loss under IN 1 W

Power dissipation per coil 0.5 W

#### Incandescent bulbs control

Max. power with incandescent lamps 1000 W

#### Installation, mounting

Mounting type din-Rail

#### Connection

Connection cross-sect. flexible conductor 1 / 4mm<sup>2</sup>

Connection cross-sect. rigid cable 1 / 4mm<sup>2</sup>

Type of connection with screw

Number of contacts 1

Type of contacts 1 changeover

Type of connection with screw terminals

#### Settings

Summer / Winter time change manual

Shortest switching time 30 mn

Type of programming analog

Programming cycle 24H

Setting Setting via day dial ; Fine setting of time via rotating hand

#### Equipment

Number of channels 1

Supply failure reserve	without
<b>Use</b>	
Cycle	daily
<b>Use conditions</b>	
Operating temperature	-10...55 °C
Working accuracy	6 mn / year