



EH210



Daily time switch without reserve with clock hands, 2 modules

Technical characteristics

Configuration

Switch mode change-over contact, usable as NC or NO

Main electrical features

Frequency 50/60 Hz

Dimensions

Depth of installed product 58 mm

Height of installed product 90 mm

Width of installed product 36 mm

Power

Power consumed 0.5 VA

Power consumption (operation) 0.5 VA

Total power loss under IN 1 W

Power dissipation per coil 0.5 W

Incandescent bulbs control

Max. power with incandescent lamps 1000 W

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 1 / 4mm²

Connection cross-sect. rigid cable 1 / 4mm²

Type of connection with screw

Number of contacts 1

Type of contacts 1 changeover

Type of connection with screw terminals

Settings

Summer / Winter time change manual

Shortest switching time 30 mn

Type of programming analog

Programming cycle 24H

Setting Setting via day dial ; Fine setting of time via rotating hand

Equipment

Number of channels 1

Supply failure reserve	without
Use	
Cycle	daily
Use conditions	
Operating temperature	-10...55 °C
Working accuracy	6 mn / year