



EC100

Hours counter

Technical characteristics

Main electrical features

| | |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 60 mm |
| Height of installed product | 90 mm |
| Width of installed product | 35 mm |

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 1.5 W |
|---------------------------|-------|

Power supply

| | |
|----------------|---------------|
| Supply voltage | 230 V +/- 15% |
|----------------|---------------|

Installation, mounting

| | |
|---------------|----------|
| Mounting type | din-Rail |
|---------------|----------|

Connection

| | |
|---|-------------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm ² |
| Connection cross-sect. rigid cable | 1,5 / 10mm ² |
| Type of connection | with screw |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...45 °C |
|-----------------------|-------------|