



EH271



## Weekly time switch with reserve with clock hands 2 modules

### Technical characteristics

#### Functions

Power reserve	≈ 200 h
---------------	---------

#### Configuration

Switch mode	change-over contact, usable as NC or NO
-------------	---

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Dimensions

Depth of installed product	58 mm
Height of installed product	90 mm
Width of installed product	36 mm

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

#### Battery

Charging time of the power reserve in hours	120
---	-----

#### Incandescent bulbs control

Max. power with incandescent lamps	1000 W
------------------------------------	--------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

#### Settings

Summer / Winter time change	manual
Shortest switching time	3.5 h
Type of programming	analog

Programming cycle

1X7D.

Setting

Fine setting of time via rotating hand

---

**Equipment**

Number of channels

1

Supply failure reserve

200 h

---

**Use**

Cycle

weekly

---

**Use conditions**

Operating temperature

-10...55 °C

Working accuracy

6 mn / year