



EH271



Weekly time switch with reserve with clock hands 2 modules

Technical characteristics

Functions

Power reserve	≈ 200 h
---------------	---------

Configuration

Switch mode	change-over contact, usable as NC or NO
-------------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	58 mm
Height of installed product	90 mm
Width of installed product	36 mm

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

Battery

Charging time of the power reserve in hours	120
---	-----

Incandescent bulbs control

Max. power with incandescent lamps	1000 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	3.5 h
Type of programming	analog

Programming cycle

1X7D.

Setting

Fine setting of time via rotating hand

Equipment

Number of channels

1

Supply failure reserve

200 h

Use

Cycle

weekly

Use conditions

Operating temperature

-10...55 °C

Working accuracy

6 mn / year