



EHN011



## Daily time switch 1 channel, 1 module with reserve

### Technical characteristics

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Power reserve	≈ 120 h
---------------	---------

#### Main electrical features

Rated operational voltage Ue	230 / 240 V
Frequency	50/60 Hz

#### Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	18 mm

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

#### Battery

Charging time of the power reserve in hours	120
---	-----

#### Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

#### Settings

Summer / Winter time change	manual
Shortest switching time	15 mn

Type of programming	analog
Programming cycle	24H
<b>Equipment</b>	
Number of channels	1
Supply failure reserve	120 h
<b>Use</b>	
Cycle	daily
<b>Safety</b>	
Protection index IP	IP20
<b>Use conditions</b>	
Operating temperature	-10...55 °C
Working accuracy	1