



EHN011



Daily time switch 1 channel, 1 module with reserve

Technical characteristics

Functions

Power reserve	≈ 120 h
---------------	---------

Configuration

Switch mode	NO contact
-------------	------------

Main electrical features

Rated operational voltage Ue	230 / 240 V
------------------------------	-------------

Frequency	50/60 Hz
-----------	----------

Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Width of installed product	18 mm
----------------------------	-------

Power

Power consumed	0.5 VA
----------------	--------

Power consumption (operation)	0.5 VA
-------------------------------	--------

Total power loss under IN	1 W
---------------------------	-----

Power dissipation per coil	0.5 W
----------------------------	-------

Battery

Charging time of the power reserve in hours	120
---	-----

Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
---	----------------------

Connection cross-sect. rigid cable	1 / 4mm ²
------------------------------------	----------------------

Type of connection	with screw
--------------------	------------

Number of contacts	1
--------------------	---

Type of contacts	1 changeover
------------------	--------------

Type of connection	with screw terminals
--------------------	----------------------

Settings

Summer / Winter time change	manual
-----------------------------	--------

Shortest switching time	15 mn
-------------------------	-------

Type of programming	analog
Programming cycle	24H
Setting	Setting via day dial

Equipment

Number of channels	1
Supply failure reserve	120 h

Use

Cycle	daily
-------	-------

Use conditions

Operating temperature	-10...55 °C
Working accuracy	1