



EHN171

Weekly time switch 1 channel, 3 modules with reserve

Technical characteristics

Functions

Power reserve	≈ 200 h
---------------	---------

Configuration

Switch mode	change-over contact, usable as NC or NO
-------------	---

Main electrical features

Rated operational voltage Ue	230 / 240 V
------------------------------	-------------

Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	54 mm

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

Battery

Charging time of the power reserve in hours	120
---	-----

Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	120 mn
Type of programming	analog
Programming cycle	1X7D.

Equipment

Number of channels	1
Supply failure reserve	120 h

Use

Cycle	weekly
-------	--------

Use conditions

Operating temperature	-10...55 °C
Working accuracy	1
