



ECP140D

## 1 Phase kWhmeter direct 40A 1M S0 MID

### Technical characteristics

#### Architecture

Type of pole	1P+N
--------------	------

#### Electric current

Rated current	40 A
Maximum measuring circuit current	40 A

#### Capacity

Number of modules	1
-------------------	---

#### Connectivity

Type of connection	Direct connection
--------------------	-------------------

#### Dimensions

Height	92 mm
Width	18 mm
Depth	60 mm

#### Main electrical attributes

Type of pulse generator	Electrical
-------------------------	------------

#### Compatibility

Suitable for	Purchase/supply
--------------	-----------------

#### Connection

Cross-section of metering input	16 - 16 mm <sup>2</sup>
Cross-section of metering output	16 - 16 mm <sup>2</sup>

#### Installation, mounting

Nominal tightening torque	1 - 1 Nm
---------------------------	----------

#### Mechanical features

Nominal tightening torque digital terminal	0.50 - 0.50 Nm
--	----------------

#### Measurement

Measuring system	Direct measurement
Type of measuring instrument	Electronic
Current measurement range	0.25 - 40.0 A
Measurement range voltage Ph-N	184 - 276 V
Frequency measuring range	45 - 65 Hz

#### Power supply

Number of phases for power supply	1
-----------------------------------	---

**Functions**

Accuracy class	B
Tariff type	One-tariff
Is calibrated	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 70 °C

**Power**

Power consumption VA	2 VA
Total power loss under IN	1 W