



EMN001



IP20

Stair case time lag switch

Technical characteristics

Configuration

Switch mode NO contact

Main electrical features

Rated operational voltage Ue 230 V

Electric current

Acceptable current rating with AC1 16 A

Dimensions

Depth of installed product 64 mm

Width of installed product 17.5 mm

Power

Max. power with fluo uncompensated lamps 3600 VA

Power consumed 1 VA

Total power loss under IN 2 W

Power dissipation per coil 0.25 W

Power supply

Supply voltage 230 V

Fluorescent bulbs control

Max. power with fluorescent parallel lamps 1000 VA

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 1 / 6mm²

Connection cross-sect. rigid cable 1,5 / 10mm²

Connection type 3 and 4 wires

Number of contacts 1

Type of contacts 1NO

Type of connection with screw terminals

Settings

Time delayed range 30s / 10min

Use conditions

Operating temperature

-10...55 °C