




EMN001



IP20

Stair case time lag switch

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Electric current

Acceptable current rating with AC1	16 A
------------------------------------	------

Dimensions

Depth of installed product	64 mm
Width of installed product	17.5 mm

Power

Max. power with fluo uncompensated lamps	3600 VA
Power consumed	1 VA
Total power loss under IN	2 W
Power dissipation per coil	0.25 W

Power supply

Supply voltage	230 V
----------------	-------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1000 VA
--	---------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Number of contacts	1
Type of contacts	1NO
Type of connection	with screw terminals

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------