



EPN515



## Latching relay 1NC+1NO 230V

### Technical characteristics

#### Main electrical features

Rated operational voltage $U_e$	250 V
---------------------------------	-------

#### Voltage

Rated insulation voltage	250 V
--------------------------	-------

#### Dimensions

Depth of installed product	63 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.5 mm
----------------------------	---------

#### Power

Total power loss under IN	1.2 W
---------------------------	-------

#### Endurance

Number of mechanical operations	500000
---------------------------------	--------

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

#### Incandescent bulbs control

Max. power with incandescent lamps	1800 W
------------------------------------	--------

#### Installation, mounting

Tightening torque	1,6Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
------------------------------------	-------------------------

Number of contacts	2
--------------------	---

Type of contacts	1NC+1NO
------------------	---------

#### Standards

Standard text	IEC/EN 60669-2
---------------	----------------

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-5...40 °C
-----------------------	------------