



ECP300C



### 3 Phase kWhmeter via CT 1A or 5A 4M S0 MID

#### Technical characteristics

#### Architecture

Number of poles	4 P
Type of pole	3P+N

#### Main electrical features

Rated operational voltage Ue	92 / 480 V
Frequency	50 Hz
Type of supply voltage	AC

#### Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

#### Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	72 mm

#### Power

Power consumed	2 VA
Total power loss under IN	0.6 W

#### Measurement

Type of measuring instrument	electronical
------------------------------	--------------

#### Power supply

Supply voltage	400 V ± 20%
----------------	-------------

#### Installation, mounting

Tightening torque	0.5Nm
Mounting type	din-Rail

#### Equipment

Type of display	retro illuminated display
Type of counter	three-phase counter with torus of measurement and impulses output

#### Standards

Standard text	EN 50470-1 / 3 ; IEC 62053-21 / 23 ; IEC 61557-12
---------------	---

#### Safety

Protection class	isol.class II
------------------	---------------

**Use conditions**

---

Operating temperature

-25...55 °C