



EPN518



Latching relay 1NC+1NO 24V

Technical Characteristics

Rated operational voltage Ue	250 V
Frequency	50/60 Hz
Rated current	16 A
Rated insulation voltage	250 V
Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	17.5 mm
Total power loss under IN	1.2 W
Number of mechanical operations	500000
Number of modules	1
Tightening torque	1,6Nm
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Number of contacts	2
Type of contacts	1NC+1NO
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-5...40 °C