



EPN518



Latching relay 1NC+1NO 24V

Technical characteristics

Main electrical features

Rated operational voltage Ue	250 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	1.2 W
---------------------------	-------

Endurance

Number of mechanical operations	500000
---------------------------------	--------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

Incandescent bulbs control

Max. power with incandescent lamps	1800 W
------------------------------------	--------

Installation, mounting

Tightening torque	1,6Nm
-------------------	-------

Connection

Type of connection	with screw
Number of contacts	2

Standards

Standard text	IEC/EN 60669-2
---------------	----------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------