



EPN519



Latching relay 1NC+1NO 12V

Technical characteristics

Main electrical features

Rated operational voltage U_e	250 V
---------------------------------	-------

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Dimensions

Depth of installed product	63 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.5 mm
----------------------------	---------

Power

Total power loss under IN	1.2 W
---------------------------	-------

Endurance

Number of mechanical operations	500000
---------------------------------	--------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

Incandescent bulbs control

Max. power with incandescent lamps	1800 W
------------------------------------	--------

Installation, mounting

Tightening torque	1,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm ²
------------------------------------	-------------------------

Number of contacts	2
--------------------	---

Type of contacts	1NC+1NO
------------------	---------

Standards

Standard text	IEC/EN 60669-2
---------------	----------------

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------