




EPN519



## Latching relay 1NC+1NO 12V

### Technical characteristics

#### Electric current

Rated current	16 A
Quiescent current	6 mA
Acceptable current rating AC1	16 A

#### Capacity

Number of modules	1
-------------------	---

#### Connection

Type of contacts	1NC+1NO
Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
Number of contacts	2

#### Voltage

Command voltage AC	12 - 12 V
Command voltage DC	0 - 0 V
Command voltage 1	12 - 12 V
Rated insulation voltage Ui	250 V
Rated operational voltage Ue	250 - 250 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Use conditions

Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Power

Total power loss under IN	1.20 W
Inrush power absorbed	25 VA

#### Dimensions

Height	83 mm
Width	17.50 mm
Depth	63 mm

#### Lighting

Max. load fluorescent lamp	800 VA
Max. load fluorescent lamp parallel compensated	900 VA
<b>Equipment</b>	
Number of NO contacts	1
Number of NC contacts	1