



ECR310D

**3 Phase kWhmeter direct 125A 6M MODBUS MID**

**Technical characteristics**

**Architecture**

Bus system	MODBUS
Type of pole	3P+N

**Electric current**

Rated current	125 A
Maximum measuring circuit current	125 A

**Capacity**

Number of modules	6
-------------------	---

**Connectivity**

Type of connection	Direct connection
Connectivity type	ModBus RS-485 3 wires

**Dimensions**

Height	92 mm
Width	107 mm
Depth	60 mm

**Main electrical attributes**

Type of pulse generator	Optical
-------------------------	---------

**Compatibility**

Suitable for	Purchase/supply
--------------	-----------------

**Connection**

Cross-section of metering input	50 - 50 mm <sup>2</sup>
Cross-section of metering output	50 - 50 mm <sup>2</sup>
Connector/plug type Bus system	Bus connection terminal

**Installation, mounting**

Nominal tightening torque	5 - 5 Nm
---------------------------	----------

**Mechanical features**

Nominal tightening torque digital terminal	0.50 - 0.50 Nm
--	----------------

**Measurement**

Measuring system	Direct measurement
Type of measuring instrument	Electronic
Current measurement range	0.25 - 125.0 A

Measurement range voltage Ph-N	92 - 276 V
Measurement range voltage Ph-Ph	160 - 480 V
Frequency measuring range	45 - 65 Hz

#### Functions

Accuracy class	B
Tariff type	T1...T2 (230V AC)/T1...T8 Modbus
Is calibrated	Yes

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Use conditions

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 70 °C

#### Power

Power consumption VA	2 VA
Total power loss under IN	0.60 W