



ERC325

Override Contactor 25A, 3NO, 230V~50Hz

Technical characteristics

Architecture

Number of poles	3 P
-----------------	-----

Main electrical features

Rated operational voltage Ue	400 V
------------------------------	-------

Frequency	50 Hz
-----------	-------

Voltage

Rated insulation voltage	440 V
--------------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	35.75 mm
----------------------------	----------

Power

Total power loss under IN	6 W
---------------------------	-----

Power dissipation per coil	1.5 W
----------------------------	-------

Endurance

Electric endurance in number of cycles	30000
--	-------

Number of mechanical operations	1000000
---------------------------------	---------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	810 VA
--	--------

Incandescent bulbs control

Max. power with incandescent lamps	1900 W
------------------------------------	--------

Connection

Number of contacts	3
--------------------	---

Equipment

Can be accessorized	Yes
---------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2X
---------------------	------

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature

-10...50 °C