



EE181

IP20

## Astronomical Time switch, 2 Channels

### Technical characteristics

#### Functions

Function	Keylock by means of blocking key
----------	----------------------------------

#### Configuration

Switch mode	2 x change-over contact
-------------	-------------------------

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Electric current

Acceptable current rating with AC1	16 A
------------------------------------	------

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	3.5 mm

#### Power

Max. power with fluo uncompensated lamps	1000 VA
Power consumed	6 VA
Incandescent bulb power	0 / 2300 W
Total power loss under IN	2 W
Power dissipation per coil	0.3 W

#### Battery

Power reserve [years]	≈ 5 a
-----------------------	-------

#### Power supply

Supply voltage	230 V
----------------	-------

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	400 VA
Max. power fluo. duo lamp comp. series	1000 W

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1,5 / 10mm <sup>2</sup>
---	-------------------------

Connection cross-sect. rigid cable	1 / 6mm <sup>2</sup>
Number of contacts	2
Type of contacts	2 changeovers contacts floating
Type of connection	with screw terminals

#### **Settings**

Summer / Winter time change	automatic
Shortest switching time	1 mn

#### **Equipment**

Number of channels	2
Supply failure reserve	5 years

#### **Use**

Cycle	weekly
-------	--------

#### **Use conditions**

Operating temperature	-10...55 °C
Working accuracy	± 1,5 s / 24H