




EE840



IP55

Motion detector infrared 360°, IP55, wall mounted, white

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Width of installed product 91 mm

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 360 °

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Lighting control

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Mounting type surface-mounted

Maximum Mounting Height 4 m

Connection

Type of connection with screw terminals

Settings

Setting with potentiometers for fine adjustment of the response brightness, sensitivity and delay time

Scope of delivery

Component with fitting material

Equipment

Angle of horizontal detection 360 °

Safety

Protection index IP IP55

Use conditions

Operating temperature

-20...55 °C