



EE861



IP55

IP55 Motion Detector Comfort 220° Anthracite

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 220 °

Materials

Colour charcoal

RAL colour RAL 7016 - Anthracite grey

Material plastic

Lighting control

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Connection

Type of connection with screw terminals

Scope of delivery

Component with fitting material

Equipment

Remote controllable EE806

Angle of horizontal detection 220 °

Safety

Protection index IP IP55

Use conditions

Operating temperature -20...55 °C