




EE861



IP55 Motion Detector Comfort 220° Anthracite

Technical characteristics

Architecture

Bus system Without

Functions

Function Presence simulation ; can be used as a single unit, main device or extension unit

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 220 °

Materials

Material plastic

Lighting control

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Connection

Type of connection with screw terminals

Settings

Setting with potentiometers for setting the response brightness and delay time without dismantling

Scope of delivery

Component with fitting material

Equipment

Remote controllable EE806

Angle of horizontal detection 220 °

Use conditions

Operating temperature -20...55 °C

