



EE861



IP55



## IP55 Motion Detector Comfort 220° Anthracite

### Technical characteristics

#### Architecture

Bus system	Without
Fixing mode	surface-mounting

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Dimensions

Height of installed product	2.5 m
-----------------------------	-------

#### Detection

Detection angle	220 °
-----------------	-------

#### Materials

Colour	charcoal
Material	plastic

#### Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

#### Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Scope of delivery

Component	with fitting material
-----------	-----------------------

#### Equipment

Remote controllable	EE806
Angle of horizontal detection	220 °

#### Safety

Protection index IP	IP55
---------------------	------

#### Use conditions

Operating temperature	-20...55 °C
-----------------------	-------------