




EE870



IP55

IP55 Motion Detector Comfort 220/360° White

Technical characteristics

Architecture

Bus system	Without
Fixing mode	surface-mounting

Functions

Function	Presence simulation ; can be used as a single unit, main device or extension unit
----------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Dimensions

Height of installed product	2.5 m
-----------------------------	-------

Power

Incandescent bulb power	2300 W
-------------------------	--------

Power supply

Supply voltage	230 V AC
----------------	----------

Detection

Detection angle	220 / 360 °
Detection angle	360 °

Materials

Colour	white
--------	-------

Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Connection

Connection type	quick connect
Type of contacts	contact floating
Type of connection	with screw terminals

Settings

Time delayed range	5s to 30 min
Setting	with potentiometers for fine adjustment of the response brightness, sensitivity and delay time

Scope of delivery

Component

with fitting material

Safety

Protection index IP

IP55

Protection class

isol.class II

Protection

with crawl-under protection

Use conditions

Operating temperature

-20...55 °C