



ESC443

Contactors 40A, 3NO+1NC, 230V~50Hz

Technical characteristics

Architecture

Number of poles	4 P
-----------------	-----

Main electrical features

Rated operational voltage Ue	400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV

Dimensions

Depth of installed product	60 mm
Height of installed product	85 mm
Width of installed product	54 mm

Power

Total power loss under IN	11.8 W
Power dissipation per coil	1.5 W

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1300 VA
--	---------

Incandescent bulbs control

Max. power with incandescent lamps	4000 W
------------------------------------	--------

Connection

Type of connection	with screw
Number of contacts	4

Equipment

Can be accessorized	Yes
---------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2X
---------------------	------

Protection class

isol.class II

Use conditions

Operating temperature

-10...50 °C