




EE871



IP55 Motion Detector Comfort 220/360° Anthracite

Technical characteristics

Architecture

Bus system Without

Functions

Function Presence simulation ; can be used as a single unit, main device or extension unit

Main electrical features

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Power

Incandescent bulb power 2300 W

Power supply

Supply voltage 230 V AC

Detection

Detection angle 220 / 360 °

Lighting control

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Connection

Connection type quick connect

Type of contacts contact floating

Type of connection with screw terminals

Settings

Time delayed range 5s to 30 min

Setting with potentiometers for fine adjustment of the response brightness, sensitivity and delay time

Scope of delivery

Component with fitting material

Safety

Protection class isol.class II

Protection

with crawl-under protection

Use conditions

Operating temperature

-20...55 °C