



ESC466

Contactors 63A, 3NO+1NC, 230V~50Hz

Technical characteristics

Architecture

| | |
|-----------------|-----|
| Number of poles | 4 P |
|-----------------|-----|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 400 V |
| Frequency | 50 Hz |

Voltage

| | |
|---------------------------------|-------|
| Rated insulation voltage | 440 V |
| Rated impulse withstand voltage | 4 kV |

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 60 mm |
| Height of installed product | 85 mm |
| Width of installed product | 54 mm |

Power

| | |
|----------------------------|--------|
| Total power loss under IN | 16.5 W |
| Power dissipation per coil | 1.5 W |

Endurance

| | |
|--|---------|
| Electric endurance in number of cycles | 30000 |
| Number of mechanical operations | 1000000 |

Fluorescent bulbs control

| | |
|--|---------|
| Max. power with fluorescent parallel lamps | 2100 VA |
|--|---------|

Incandescent bulbs control

| | |
|------------------------------------|--------|
| Max. power with incandescent lamps | 6500 W |
|------------------------------------|--------|

Connection

| | |
|--------------------|---|
| Number of contacts | 4 |
|--------------------|---|

Equipment

| | |
|---------------------|-----|
| Can be accessorized | Yes |
|---------------------|-----|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|---------------|
| Protection index IP | IP2X |
| Protection class | isol.class II |

Use conditions

Operating temperature

-10...50 °C